


Product Datasheet - Technical Specifications



More information in our Web-Shop at **www.meilhaus.com** and in our download section.

Your contact

Technical and commercial sales, price information, quotations, demo/test equipment, consulting:

Tel.: +49 - 81 41 - 52 71-0

FAX: +49 - 81 41 - 52 71-129

E-Mail: sales@meilhaus.com

Downloads:

www.meilhaus.com/en/infos/download.htm

Meilhaus Electronic GmbH | Am Sonnenlicht 2 82239 Alling/Germany

 Tel.
 +49 - 81 41 - 52 71-0

 Fax
 +49 - 81 41 - 52 71-129

 E-Mail
 sales@meilhaus.com

Mentioned company and product names may be registered trademarks of the respective companies. Prices in Euro plus VAT. Errors and omissions excepted.

© Meilhaus Electronic.

LAN GPIB GATEWAY

DESCRIPTION

ICS's 9065 is an Ethernet-to-GPIB Gateway that lets you easily control your GPIB instruments from any PC, over an in-house network or anywhere in the world over the internet. The 9065 connects to any TCP/IP network or to a network port on your computer.

The 9065 is a VXI-11 compliant

network service which can be easily controlled by several programming techniques. Windows users can control the 9065 through VISA layers from Agilent, National Instruments, Kikusui and other vendors. Apple OS X, Unix, and Linux operating system users can control the 9065 with RPC (Remote Procedure Call) calls over a TCP/IP network. RPC provides an invisible communication medium allowing the developer to concentrate on his program and eliminates driver problems caused by kernel or OS variations.

The 9065's internal webserver includes an interactive html Control page so the user can control GPIB instruments directly from a web browser.

ICS also provides a VXI-11 Keyboard utility for Windows that lets users find and control GPIB instruments connected to the 9065.

VXI-11

VXI-11 is a communication standard developed in conjunction with the VISA Specification for instruments and for GPIB Gateways (Controllers) like ICS's 9065. VXI-11 provides an error free, GPIB like experience for controlling instruments over an Ethernet network while maintaining the IEEE-488.2 Standard.




Figure 1 9065 shown connected to Company Network



9065 Ethernet-to-GPIB Gateway

Programming

If you program with Agilent VEE or other Agilent programs, you can use Agilent's VISA or its internal SICL library to control ICS's 9065. The Model 9065 is fully VXI-11 compliant and is interchangeable with Agilent's' E5810A and older E2050B if you are not using their RS-232 interfaces or their private commands. Agilent's VISA or its internal SICL library is recommended for C/C++/C# and Visual Basic programmers.

LabVIEW and National Instruments' VISA supports the 9065 with VXI-11.3 calls. NI's Measurement and Automation Explorer treats the 9065 as any other TCP/IP resource¹.

Apple's OS X, Linux or any variation of Unix like SunOS, IBM-AIX, or HP-UX, can communicate with the 9065's RPC Service either through RPC over TCP/IP or, in some cases, with VISA calls.

If you program with Java, then you can write a 9065 control program that can be easily moved to virtually any operating system. The Java jGpibEnet project on SourceForge was developed using an ICS 8065 Controller. ICS provides numerous Application Notes about programming

the 8065 and 9065.

For Python users, PyVXI-11 is a new Python and C++11 extension that supports communications between a computer and instruments. PyVXI-11 relies heavily on the 9065 Gateway and is a modern pythonic alternative to LabView and Linux GPIB.

9065

Ethernet-to-GPIB Gateway

- Control GPIB instruments anywhere from any PC Control GPIB and HP-IB Devices anywhere there is a network connection.
- Runs from any VXI-11 compliant VISA library.
 Use VEE, LabVIEW, C, and Visual Basic programs with VISA or SICL calls.
- Adds GPIB Controller capability to MAC OS X, Unix, Linux, SunOS and similar operating systems. RPC calls over TCP/IP eliminates all driver problems.
- Control GPIB instruments with any web browser.
 New interactive HTML page for controlling instruments
- ICS's VXI-11 Keyboard Controller program provides interactive control of GPIB devices.
 - Lets you control instruments without writing a program.
- Online programming support.
 Numerous Application Notes for all programming methods.
- Model 8065 replacement.
 Faster plus an improved webserver and control page.

RoHS Compliant

(€ Approved



RPC Calls eliminate Drivers

Apple OS X, Unix and Linux systems do not need special drivers when using RPC calls to communicate with the 9065. These operating systems include an rpcgen utility that converts the VXI-11 Specification's RPCL header file into operating system specific library files that can be called from a C language program. Using the operating system's rpcgen utility eliminates driver bugs and driver obsolescence when the test computer is updated or when the test program gets ported to another system. ICS has several Application Notes that show how to write programs with RPC calls. RPC calls can be used on Windows PCs with a third party RPC utility.

New HTML Control Page

The 9065's webserver includes an Instrument Control Page that lets a user control instruments connected to the 9065 with a web browser. The 9065 Control Page shown in Figure 2, lets a user write out commands and automatically reads back the instrument responses. The page operates with auto query enabled so it automatically detects most queries and serves up the instrument responses. This prevents the user from getting out of sync with the instrument

The Control Page also includes the common GPIB commands such as Device Trigger, Device Clear and Serial Poll. Its important to include these commands on the Control Page to control instruments that use them as escape characters, to clear buffers, to initiate an action and to read the device status register.

Keyboard Controller Program

The 9065 includes ICS's VXI-11 Keyboard program for Windows which provides interactive control of GPIB devices from the computer keyboard without having to write a program. The VXI-11 Keyboard program uses ICS's VXI-11.dll for Windows PCs and is the ideal utility program for testing the 9065 Controller, for exercising GPIB devices or for trying out device commands before using them in a program.

With the VXI-11 Keyboard program you can find the 9065 on your network, link to your 9065s, read back Bus Status, generate IFCs, run the 488.2 FindLstn protocol to discover the GPIB devices connected to the 9065, and link to an instrument. Besides reading and writing data strings, the VXI-11 Keyboard has controls for Device Clear, Device Trigger, and Serial Poll. Instrument links can be locked manually or automatically to prevent another user from interfering with your use of the GPIB devices.

Ease of Installation

ICS's 9065 is very easy to install. Plug the 9065 into a network access point (switch or hub) adjacent to your computer as shown in Figure 4 or use an Ethernet cable to connect the 9065 directly to a PC's network port. Then use your favorite web browser or run ICS's Configuration Utility to configure the unit for your network. Both let you set the 9065 to a static IP address or you can enable the 9065 to accept an DHCP address setting if your network has a server that can assign network addresses. Then set the remaining network and GPIB bus parameters. Save the setup and the 9065 is ready to go.




Figure 2 9065 Control Page




Figure 3 VXI-11 Keyboard Utility




Figure 4 9065 Installation Setup Connection

Note: 1. Problems with NI-VISA version 5.2 and later prevent it and MAX from recognizing ICS and Agilent Ethernet Gateways. Recommend using version 5.1 or earlier versions until the problem is resolved.

Multiuser Capabilities

ICS's 9065 Ethernet to GPIB Controller lets multiple users share equipment from anywhere in the world at anytime.

Figure 5 on the right shows a 9065 being used to control a rack of test instruments on a factory test floor. The test technician's computer and the 9065 are both connected to a local network hub or switch. The test program is normally run in the test technician's computer.

When the Test Engineer has to upgrade or modify the test program he can run the new program from his computer and make any necessary changes without having to have a duplicate set of the production test equipment in his lab. This is a significant cost savings.

The Field Engineer can use the company's Virtual Private Network (VPN) to gain access to the company's network over the Internet. He too can become a 9065 client with out impacting the test setup. In companies with multiple test locations, VPN connections can allow the Test Engineer to access and update test programs anywhere in the world from his home office.

In a test environment, the Engineering and Field Engineer would normally not access the Test Equipment at the same time that it was being used by the Test Technician. However, in other applications with remote data collection equipment, such as in a weather station, the instruments could be accessed by several clients at the same time. Here one client may be looking at a data logger while another client could be reading current conditions. The 9065 supports multiple clients using different instruments at the same time and includes locking to prevent accidental access while an instrument is in use.

9065 Advantages

ICS's 9065 is a newer, faster Gateway that replaces the Model 8065 with a faster processor and Ethernet interface. The 9065 is a 100 percent VXI-11.2 and VXI-11.3 compatible and provides complete GPIB control capability and the ability to implement the IEEE-488.2 Controller Protocols like FindLstn. Other competitive units only have VXI-11.3 capability.

The 9065 supports SRQ handling, serial polling and SRQ notify. The 9065 also supports multiple clients as part of its standard firmware making it easy to share equipment from remote locations.




Figure 5 9065 Multi-user Application

The 9065 is a universal controller since it is not limited by the availability of a driver for a specific operating system. Moreover, the resulting test programs are more robust since they are free of any driver bugs. Finally the 9065 is RoHS compliant and meets most countries' environmental specifications.

Hardware

ICS's 9065 Controller is packaged in ICS's small metal Minibox™ case that provides proven EMI/RFI protection and rack mount capability. Rear panel RJ-45 and GPIB connectors provide access to the network and to the GPIB bus. Front panel LEDs provide visual indication of the network and GPIB bus status and diagnostic help for troubleshooting system problems.

One or two 9065s can be rack mounted in a 1 U high space. Chose a single rack kit that holds one unit or a dual rack kit that holds two units.

Network Communication

The client application uses the VXI-11 or RPC protocol to communicate with the 9065 and to control and transfer data to and from GPIB instruments. Both protocols operate over a TCP/IP network and guarantee error free communication with the 9065. The 9065 has communication timeout and keepalive capability to maintain the communication link with the client application. When the 9065 discovers that the channel is no longer active, or when a channel is closed, it closes that channel and releases all resources that were used by the client. This unlocks any instruments links, destroys the links and returns all resources to the pool for the next user.

An auto-disconnect feature is included in the 9065 for compatibility with programs designed for the Agilent (HP) E5810A and E2050B LAN to GPIB Controllers. If the user enables auto-disconnect, the channel is aborted automatically whenever the link count goes to zero.

Supported Standards

IEEE 488.1 Capabilities:

The 9065 meets IEEE-STD-488.1 with the following capabilities:

AH1, SH1, C1, C2, C3, C4, and C9 E2 Drivers incorporate power up/down protection and drive 14 devices.

IEEE 488.2 Compatible

Runs all required 488.2 controller protocols and includes bus signal line monitoring.

488 Bus Performance

Long term GPIB transfer rates are limited by the LAN data transfer rate, the Client-computer performance and the GPIB device. Short term 9065 data rates are:

GPIB to 9065 > 125 kbytes/s 9065 to GPIB > 180 kbytes/s

GPIB Drivers 14 loads or devices Device Address 64 addresses-any combina-

> tion of primary or primary and secondary addresses.

9065 address 0 to 30 [0]

VXI-11 Capabilities

Fully VXI-11.2 and VXI-11.3 compliant VXI-11.2 Interface Control VXI-11.3 Device Control

Clients 1 to 15

Channel types Data, Abort and Interrupt

Instrument links 64 max

RPC Protocol

Conforms to ONC RPC Version 2

Ethernet Interface

IEEE 802.3 compliant Type Speeds 10BaseT (10 Mb/s) 100BaseT (100 Mb/s)

IP Address Static or DHCP w/AutoIP Factory setting 192.168.0.254 static

Interface name any [gpib0]

Internal WebServer

The internal WebServer provides HTML web pages for configuring the 9065 and for controlling GPIB instruments.

System Requirements

Computer with an IEEE 802.3 LAN interface. Requires RPC support or a VXI-11 compliant VISA layer installed.

Supported Software

The 9065 supports the following application and program languages:

NI LabVIEW (5.1 thru 8.6)

Agilent VEE - IO Libraries 14.2 and later

MathWorks MathLab Visual Basic 6.0* Visual Basic .NET (2005)* Visual C, C++ and C#* Java*

* with VISA or RPC calls

Controls and Indicators

Power Front-panel switch LAN Reset Rear-panel push-button

LEDs

PWR Power on LNK Unit connected to an active LAN ACT Transferring messages to/ from the network RDY Unit has passed self test

Unit is addressed to talk **TALK LSTN** Unit is addressed to listen SRO asserted on GPIB bus **SRQ ERR** Unit has detected a soft

Physical

Size 7.45" L x 5.57" W x 1.52" H (18.92 cm L x 14.15 cm W x 3.86 cm H)

Weight 1.6 lbs. (0.73 kg.)

plus power adapter

Construction **RoHS** Compliant

Temperature

-10 °C to +65 °C Operating Storage -40 °C to + 70 °C

Humidity 0-90% RH non-condensing

Shock/Vibration Normal handling

Connectors

GPIB GPIB 24 pin ribbon

with metric studs.

Ethernet RJ-45

Power 9 to 32 Vdc @ 4 VA

RFI/EMI CE Certified

EN 61000-6-4:2001. **EEC Standards**

> EN 61000-6-2:2001. EN 55024:1998. and EN 55022:1998.

Included Accessories

Instruction Manual

CD-ROM with VXI-11 Keyboard Controller program and Configuration Utility.

LAN Crossover Cable.

UL/CSA/VDE approved AC power Adapters provided for:

US - 115±10% Vac, 60 Hz (std.)

-U Europe/UK/Australia/China/Japan plugs,

100 to 240 Vac, 50/60 Hz

ORDERING INFORMATION

GPIB Accessary Cables

Part Number

Ethernet - GPIB Controller with 115 VAC adapter, Manual and CD-ROM

9065 9065-U

Ethernet - GPIB Controller with 100-240 VAC adapter with UK, Europe and Australia/China plugs, Manual and CD-ROM

See separate data sheet

Rack Mounting Kits (holds one or two 9065s). See separate data sheet

Single - 114210, Dual - 114211